

Garant

Grooving insert medium machining, HB7020, Groove width w (mm) / quantity: 3/50

**Order data**

Order number	GG2740 3/50
GTIN	4067263097617
Item class	GGN

Technical description

Tolerance groove width w	± 0.03 mm
Corner radius R	0.2 mm
Quantity	50
Contents	273725 3
Cutting depth a_p	0.8 - 1.7 mm
Feed f	0.1 - 0.23 mm/rev.
Grade	HB7020
Main application	P
Secondary application	M
Type of product	Indexable insert for grooving

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	220 m/min	P
Steel < 750 N/mm ²	suitable	180 m/min	P
Steel < 900 N/mm ²	suitable	170 m/min	P
Steel < 1100 N/mm ²	suitable	140 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	120 m/min	P
INOX < 900 N/mm ²	suitable	140 m/min	M
INOX > 900 N/mm ²	suitable	130 m/min	M
Ti > 850 N/mm ²	suitable	60 m/min	S
GG(G)	suitable	200 m/min	K
CuZn	suitable	250 m/min	N
Uni	suitable		
continuous	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

Grooving insertmedium machining Groove width w 3 mm

273725 3