

Garant**Turning insert, medium machining DCGT, HB7310, Size / quantity: 11T304/50****Order data**

Order number	GG2675 11T304/50
GTIN	4067263098126
Item class	GGN

Technical description

Feed f	0.1 - 0.3 mm/rev.
Contents	260462 HB7310
Cutting depth a_p	0.25 - 2.75 mm
Cutting speed v_c main application	250 - 600 mm/min
Quantity	50
ISO code indexable insert	DCGT11T304
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

DC.T 11T304 Grade HB7310

260462 HB7310