

**Garant****Turning insert, medium machining DCGT, HU7310, Size / quantity: 11T302/50****Order data**

Order number	GG2672 11T302/50
GTIN	4067263098003
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	350 - 600 mm/min
Contents	260458 HU7310
Feed $f$	0.1 - 0.3 mm/rev.
Cutting depth $a_p$	0.15 - 2.75 mm
Quantity	50
ISO code indexable insert	DCGT11T302
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

## Accessories

DC.T 11T302 Grade HU7310

260458 HU7310