

**Garant****Turning insert, medium machining DCGT, HB7310, Size / quantity: 11T302/30****Order data**

Order number	GG2675 11T302/30
GTIN	4067263098096
Item class	GGN

**Technical description**

Feed f	0.1 - 0.3 mm/rev.
Cutting speed $v_c$ main application	250 - 600 mm/min
Cutting depth $a_p$	0.15 - 2.75 mm
Contents	260458 HB7310
Quantity	30
ISO code indexable insert	DCGT11T302
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

## Accessories

DC.T 11T302 Grade HB7310

260458 HB7310