

Garant**Turning insert, medium machining VBGT, HU7310, Size / quantity: 160408/30****Order data**

Order number	GG2681 160408/30
GTIN	4067263098454
Item class	GGN

Technical description

Contents	261234 HU7310
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 2.5 mm
Quantity	30
Cutting speed v_c main application	350 - 600 mm/min
ISO code indexable insert	VBGT160408
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VB.T 160408 Grade HU7310

261234 HU7310