

**Garant****Turning insert, medium machining VBGT, HU7310, Size / quantity: 110304/50****Order data**

|              |                  |
|--------------|------------------|
| Order number | GG2681 110304/50 |
| GTIN         | 4067263098423    |
| Item class   | GGN              |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| Quantity                             | 50                           |
| Cutting speed $v_c$ main application | 350 - 600 mm/min             |
| Feed $f$                             | 0.1 - 0.3 mm/rev.            |
| Contents                             | 261224 HU7310                |
| Cutting depth $a_p$                  | 0.25 - 1.75 mm               |
| ISO code indexable insert            | VBGT110304                   |
| Grade                                | HU7310                       |
| Chip breaker                         | AM                           |
| Type of product                      | Indexable insert for turning |

## Accessories

VB.T 110304 Grade HU7310

261224 HU7310