

Garant**Turning insert, medium machining VBGT, HU7310, Size / quantity: 160404/30****Order data**

Order number	GG2681 160404/30
GTIN	4067263098430
Item class	GGN

Technical description

Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.25 - 2.5 mm
Contents	261232 HU7310
Quantity	30
Cutting speed v_c main application	350 - 600 mm/min
ISO code indexable insert	VBGT160404
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VB.T 160404 Grade HU7310

261232 HU7310