

Garant**Turning insert, medium machining VBGT, HU7310, Size / quantity: 110301/50****Order data**

Order number	GG2681 110301/50
GTIN	4067263098386
Item class	GGN

Technical description

Quantity	50
Cutting depth a_p	0.05 - 1.75 mm
Contents	261220 HU7310
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
ISO code indexable insert	VBGT110301
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VBGT 110301 Grade HU7310

261220 HU7310