

**Garant**
**HiPer-Drill base body, 8×D, Ø DC: 13,5mm**

**Order data**

Order number	231615 13,5
GTIN	4045197603173
Item class	21S

**Description**
**Version:**

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

**Application:**

For stationary and rotating use. For holes up to IT9 accuracy.

**Recommendation:**

Drill the pilot hole.

**Note:**

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

reduce  $v_f$  values by 20 %.

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

For process reliability when using the drill, initial pilot drilling to 1.5×D with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

**Technical description**

Shank Ø $D_s$	16 mm
Dia. range $D_c$	13.5 - 13.99 mm
Clamping screw	231999 71P (0.6 Nm)

Reach L <sub>1</sub>	112 mm
Shank length L <sub>s</sub>	48 mm
Series	HiPer-Drill
Number of cutting edges Z	2
Overall length L	183 mm
Version	8xD
Shank	ISO 9766
Use for drilling	limited drilling with oblique exit
Use for drilling	limited drilling through a stack
Use for drilling	limited oblique spot drilling
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

Torx Plus® screw Drive 7IP	231999 7IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 7IP	674252 7IP
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6