

Garant**Turning insert, medium machining VCGT, HB7310, Size / quantity: 160404/50****Order data**

Order number	GG2689 160404/50
GTIN	4067263098744
Item class	GGN

Technical description

Contents	261458 HB7310
Cutting speed v_c main application	250 - 600 mm/min
Cutting depth a_p	0.25 - 2.5 mm
Feed f	0.1 - 0.3 mm/rev.
Quantity	50
ISO code indexable insert	VCGT160404
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VC.T 160404 Grade HB7310

261458 HB7310