

## Garant

Blade HSS width  $a_p = 2.2$  mm,  $\varnothing D$  / number of teeth Z: 63/4mm



### Order data

Order number	218442 63/4
GTIN	4045197534125
Item class	21P

### Description

#### Version:

High-performance parting-off milling cutter system with choice of either collar and **low-cost steel blade** or collar and **high-precision temperature-resistant HSS blade**.

#### Application:

For slitting and parting off milling. For high repetition accuracy in series production it is preferable to use the HSS blade.

#### Attention:

Please order the assembly key No. 279940 separately.

#### Note:

Side and parting-off milling cutters available up to  $\varnothing D = 200$  mm.  
HSS spare blades can be reordered as accessories.

### Technical description

Set of fastening screws	219985
suitable indexable insert	XC.. 1119
Cutting edge $\varnothing D_c$	63 mm

Number of cutting edges Z	4
Shank type	with bore
Tool material	HSS
Type of product	Side milling cutter

---

## Accessories

Securing screw set 10 pieces	219985
------------------------------	--------