

Garant**Turning insert, medium machining VCGT, HU7310, Size / quantity: 110304/50****Order data**

Order number	GG2686 110304/50
GTIN	4067263098607
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 1.75 mm
Contents	261454 HU7310
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
Quantity	50
ISO code indexable insert	VCGT110304
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VC.T 110304 Grade HU7310

261454 HU7310