

**Garant****Turning insert, medium machining VCGT, HU7310, Size / quantity: 160404/30****Order data**

Order number	GG2686 160404/30
GTIN	4067263098638
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.25 - 2.5 mm
Cutting speed $v_c$ main application	350 - 600 mm/min
Contents	261458 HU7310
Feed $f$	0.1 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	VCGT160404
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

## Accessories

VC.T 160404 Grade HU7310

261458 HU7310