

**Garant****Turning insert, medium machining VCGT, HB7310, Size / quantity: 160408/50****Order data**

Order number	GG2689 160408/50
GTIN	4067263098768
Item class	GGN

**Technical description**

Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_p$	0.55 - 2.5 mm
Cutting speed $v_c$ main application	250 - 600 mm/min
Contents	261459 HB7310
Quantity	50
ISO code indexable insert	VCGT160408
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

## Accessories

VC.T 160408 Grade HB7310

261459 HB7310