

**Garant**
**Copy milling head, hard machining, HB7730, Ø D h10: 10mm**

**Order data**

Order number	210370 10
GTIN	4045197523464
Item class	21M

**Technical description**

Head length l	13 mm
Flute length L <sub>2</sub>	7.5 mm
Cutter Ø D	10 mm
maximum cutting depth a <sub>p max</sub> in steel < 60 HRC	0.3 mm
Arbor size	10 mm
Free length	13 mm
Feed f <sub>z</sub> for copy milling in steel < 60 HRC	0.04 mm
Number of cutting edges Z	4
Series	TopCut
Grade	HB7730
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Helix angle	15 degrees
Direction of infeed	horizontal and oblique

Cutting width $a_e$ for milling operation	0.05×D for copy milling
Through-coolant	no
suitable arbor	GARANT TopCut
Type of product	Cutter insert for milling

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	50 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	40 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	S
GG(G)	suitable	160 m/min	K
Oil	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

---

**Accessories**

Plug-in adapter for torque wrench Type 8X3	219986 8X3
Assembly wrench Type 8X3	219987 8X3