

Garant

Blade HSS width $a_p = 2.2$ mm, $\varnothing D$ / number of teeth Z: 100/8mm



Order data

| | |
|--------------|---------------|
| Order number | 218442 100/8 |
| GTIN | 4045197534149 |
| Item class | 21P |

Description

Version:

High-performance parting-off milling cutter system with choice of either collar and **low-cost steel blade** or collar and **high-precision temperature-resistant HSS blade**.

Application:

For slitting and parting off milling. For high repetition accuracy in series production it is preferable to use the HSS blade.

Attention:

Please order the assembly key No. 279940 separately.

Note:

Side and parting-off milling cutters available up to $\varnothing D = 200$ mm.
HSS spare blades can be reordered as accessories.

Technical description

| | |
|--------------------------------|-----------|
| Cutting edge $\varnothing D_c$ | 100 mm |
| Set of securing screws | 219985 |
| suitable indexable insert | XC.. 1119 |

| | |
|---------------------------|---------------------|
| Number of cutting edges Z | 8 |
| Shank type | with bore |
| Tool material | HSS |
| Type of product | Side milling cutter |

Accessories

| | |
|------------------------------|--------|
| Securing screw set 10 pieces | 219985 |
|------------------------------|--------|