



Side milling cutter with collar Width $a_p = 5$ mm, $\varnothing D: 80$ _ mm

Order data

Order number	218562 80_
GTIN	4045197462282
Item class	210

Description

Version:

Side milling cutters of robust special steel for reduced vibration.

Description:

Side milling cutters with collar of robust special steel for reduced vibration. For grooving and slotting. No. 219949 (TX9; 2.0 Nm). Further sizes on request.

Application:

For milling grooves and slots.

Achievable base of the slot = 176° (not flat).

Spare part:

No. 219949 (TX9; 2.0 Nm).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2**, with bit No. **674248 size TX9**.

Side milling cutters available up to $\varnothing D = 200$ mm.

Through-coolant: false

Tool exchange: PowerCard

ISO code indexable insert: SN.. 1103

Pack of insert screws: 219949 (TX9; 2.0 Nm)

Technical description

Through-coolant	no
Tool material	
Shank type	
Width a_p	5 mm
Tool exchange	PowerCard
Pack of insert screws	219949 (TX9; 2.0 Nm)

ISO code indexable insert	SN.. 1103
Norm	
Machining strategy	
Coating	
Type of product	