

Garant

**Parallel arbor, with through-coolant, Weldon shank, for cutter head Ø D:
10mm**



Order data

| | |
|--------------|---------------|
| Order number | 210557 10 |
| GTIN | 4045197557735 |
| Item class | 21Z |

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

| | |
|-------------------------------|--------------|
| Reach L_1 | 24 mm |
| for cutter head Ø D | 10 mm |
| External Ø d_1 | 9.8 mm |
| recommended tightening torque | 5 Nm |
| Overall length L | 75 mm |
| Shank Ø D_s | 16 mm |
| Series | TopCut |
| Adapter | Weldon shank |
| Through-coolant | yes |

Type of product

Threaded copy mill arbor