

**Garant**
**Chamfering milling head, 90°, HB730, Ø D ± 0.01: 12mm**

**Order data**

Order number	210390 12
GTIN	4045197523525
Item class	21M

**Technical description**

Head length l	16 mm
Flute length L <sub>2</sub>	8.5 mm
Cutter Ø D	12 mm
maximum cutting depth a <sub>p,max</sub> in steel < 900 N/mm <sup>2</sup>	4 mm
Corner chamfer angle	45 degrees
Arbor size	12 mm
Feed f <sub>z</sub> in steel < 900 N/mm <sup>2</sup>	0.08 mm
maximum cutting depth a <sub>p,max</sub> when slot milling from solid	6
Overall length L	30.1 mm
Number of cutting edges Z	3
Series	TopCut
Grade	HB730
Tool material	Solid carbide
Countersink tip angle	90
Standard	Manufacturer's standard

Type	N
Direction of infeed	horizontal
Through-coolant	no
Shank type	GARANT TopCut
Type of product	Threaded copy milling cutter

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	50 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	40 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	S
GG(G)	suitable	160 m/min	K
Oil	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air	suitable
-----	----------

---

## Accessories

Plug-in adapter for torque wrench Type 10X4	219986 10X4
---	-------------

Assembly wrench Type 10X4	219987 10X4
---------------------------	-------------