

**Garant**
**NC spotting drill 142°, HB730, Ø D ± 0.01: 16mm**


### Order data

Order number	210405 16
GTIN	4045197607744
Item class	21M

### Technical description

Milling head Ø D	16 mm
Head length l	20 mm
Feed f in steel < 900 N/mm <sup>2</sup>	0.8 mm/rev.
Arbor size	16 mm
Series	TopCut
Grade	HB730
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Number of cutting edges Z	2
Point angle	142 degrees
Shank	GARANT TopCut
Through-coolant	no
Type of product	Cutter insert for centre drilling and spot drilling

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	50 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	40 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	S
GG(G)	suitable	160 m/min	K
Oil	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

## Accessories

Plug-in adapter for torque wrench Type 13X4	219986 13X4
Assembly wrench Type 13X4	219987 13X4

