

Extension cable, 250 V, Type: 10N



Order data

Order number	081182 10N
GTIN	4003644009312
Item class	08B

Description

Version:

Certified for exterior use and for use in humid environments (IP44). Resistant to oil, petrol, UV radiation.

Neoprene rubber cable with splash-proof rubber plug and socket.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Cable structure	3G1.5
Type	10N
Cable length	10 m
Cable class	H07RN-F
Material cable	Neoprene
impact-resistant and splash-proof	Category 2 (K2) to BGI

IP Index of Protection	IP 44
Power supply	Mains operated
Plug type, input	F
Product name attribute	250 V
AC supply voltage	250 V
Type of product	Extension cable

Accessories

CableFix cable suspension system Type L	081191 L
CableFix cable suspension system Type S	081191 S
CableFix cable suspension system Type XL	081191 XL