



## Side milling cutter with collar Width $a_p = 6 \text{ mm}$ , $\varnothing D: 50 \text{ mm}$

### Order data

Order number	218564 50_
GTIN	4045197462305
Item class	210

### Description

#### Version:

Side milling cutters of robust special steel for reduced vibration.

#### Description:

Side milling cutters with collar of robust special steel for reduced vibration. For grooving and slotting. No. 219950 (TX15; 2.2 Nm). Further sizes on request.

#### Application:

For milling grooves and slots.

Achievable base of the slot =  $176^\circ$  (not flat).

#### Spare part:

No. 219950 (TX15; 2.2 Nm).

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674248 size TX15**.

Side milling cutters available up to  $\varnothing D = 200 \text{ mm}$ .

Through-coolant: false

Tool exchange: PowerCard

ISO code indexable insert: SN.. 1203

Pack of insert screws: 219950 (TX15; 2.2 Nm)

### Technical description

Tool material	
Through-coolant	no
Shank type	
Tool exchange	PowerCard
Width $a_p$	6 mm
Pack of insert screws	219950 (TX15; 2.2 Nm)

ISO code indexable insert	SN.. 1203
Machining strategy	
Coating	
Norm	
Type of product	