



HELI3MILL shoulder mill, with bore, \varnothing DC / number of effective cutting edges Z: 125/7mm



Order data

Order number	226490 125/7
GTIN	7291075313123
Item class	19D

Description

Version:

Reliable shoulder milling system for a wide range of applications. Versions in two system sizes with cutting edge lengths in 10 and 15 mm. Optimally supported Trigon indexable inserts in the seat ensure true 90° shoulders. Ideally suited for circular interpolation milling operations and ramping.

Spare part:

Pack of insert screws No. **229696 2** (IP20; 9.0 Nm).

Technical description

suitable indexable insert	TD..1505..
Ramping length L for α_{\max}	1501.11 mm
\varnothing D ₃	120.6 mm
Overall length L _{tot}	63 mm
Circular interpolation milling \varnothing D _{max}	249 mm

Number of cutting edges Z	7
Circular interpolation milling a_p	3.3 mm
Series	HELI3MILL
Circular interpolation milling $\varnothing D_{\min}$	245 mm
Mounting bore \varnothing	40 mm
Ramping angle α_{\max}	0.5 degrees
Cutting edge $\varnothing D_c$	125 mm
Manufacturer's designation	HM390 FTD D125-7-40-15
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Plunging
Milling application	Plunging
Milling application	Ramping
Through-coolant	yes
Machining strategy	HPC
Type of product	End / face mill

Accessories

Set of insert screws 10 pieces Type 2	229696 2
---------------------------------------	----------