

Garant GRIDLINE

**Tool cabinet complete with drawers 75 kg, 20×20G, Height mm / number of drawers: 900/7****Order data**

Order number	930505 900/7
GTIN	4067263100621
Item class	9GK

**Description****Version:**

Completely equipped tool cabinet in 24×24G, with drawers 20×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

Drawer usable area in G	20×20
Usable height for drawers	800 mm
Depth	600 mm

Number of doors	0
Electronic locking system can be retrofitted	yes
Base cabinet underneath height-adjustable workstation	no
Weight	105 kg
Width	600 mm
Height	900 mm
Drawer usable depth	500 mm
Usable height	800 mm
Drawer usable depth in G	20
Number of drawers	7
Drawer usable width	500 mm
Number of pull-out shelves	0
Drawer usable width in G	20
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Tool cabinet