



HELI3MILL shoulder mill, with bore, Ø DC / number of effective cutting edges Z: 50/4mm



Order data

Order number	226490 50/4
GTIN	7291075313048
Item class	19D

Description

Version:

Reliable shoulder milling system for a wide range of applications. Versions in two system sizes with cutting edge lengths in 10 and 15 mm. Optimally supported Trigon indexable inserts in the seat ensure true 90° shoulders. Ideally suited for circular interpolation milling operations and ramping.

Spare part:

Pack of insert screws No. **229696 1** (IP20; 9.0 Nm).

Technical description

Overall length L_{tot}	40 mm
Circular interpolation milling a_p	3.9 mm
Circular interpolation milling Ø D_{min}	95 mm
suitable indexable insert	TD..1505..
Ramping length L for α_{max}	468.99 mm

Number of cutting edges Z	4
Circular interpolation milling $\varnothing D_{\max}$	99 mm
Series	HELI3MILL
Mounting bore \varnothing	22 mm
Ramping angle α_{\max}	1.6 degrees
$\varnothing D_3$	45.6 mm
Cutting edge $\varnothing D_c$	50 mm
Manufacturer's designation	HM390 FTD D050-4-22-15
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Plunging
Milling application	Plunging
Milling application	Ramping
Through-coolant	yes
Machining strategy	HPC
Type of product	End / face mill

Accessories

Set of insert screws 10 pieces Type 1	229696 1
---------------------------------------	----------