

Garant GRIDLINE

**Tool cabinet complete with drawers 75 kg, 36×24G, Height mm / number of drawers: 800/7A****Order data**

Order number	931305 800/7A
GTIN	4067263101000
Item class	9GK

**Description****Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

Usable height for drawers	700 mm
Height	800 mm
Drawer usable depth	600 mm
Electronic locking system can be retrofitted	yes

Weight	162 kg
Number of doors	0
Number of drawers	7
Width	1000 mm
Drawer usable depth in G	24
Depth	700 mm
Drawer usable area in G	36×24
Usable height	700 mm
Base cabinet underneath height-adjustable workstation	no
Drawer usable width	900 mm
Number of pull-out shelves	0
Drawer usable width in G	36
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet