



## ISCAR SUMOCHAM drilling head ICP-2M k7, IC908, Ø DC: 15,5mm



### Order data

Order number	231742 15,5
GTIN	7291075287448
Item class	23J

### Description

#### Version:

**Vee ground** drilling head for precise positioning and stable seating. Angled, **radial stop surfaces** for a significant increase in clamping force due to the cutting forces acting during machining. For productive drilling with **high feed rates**.

#### ICP-2M

Main area of application **ISO P**. Higher accuracy and better surface quality due to **4 guide chamfers**. Optimum roundness of the bore, low axial forces, increased stability, increased metal removal rate.

#### Note:

Cutting data applies for the base body 5×D. Drill pilot holes exclusively with drilling head of the same type – in particular for drilling heads FCP and QCP-2M. Please observe the application instructions for the base body. Cutting tolerance of the inserts: **k7** (positive toleranced cutting edge diameter).

Designation convention: [type] [Ø D<sub>c</sub>]-[addition] [cutting material]

Examples:

No. 231740 6.5 ICP 065 IC908

No. 231742 18.5 ICP 185-2M IC908

No. 231745 18.5 HCP 185-IQ IC908 **The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.**

## Technical description

Ø D	15.5 mm
for base body size	15
Series	SUMOCHAM
Feed f in steel < 900 N/mm <sup>2</sup>	0.26 mm/rev.
Coating	TiAlN
Number of changes/inserts	2
Iscar item designation	ICP 155-2M IC908
Geometry	ICP-2M
Point angle	154 degrees
Manufacturer's designation	ICP 155-2M IC908
Grade	IC908
Tool material	Carbide
Type of product	Drilling head for boring

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	55 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
Steel < 60 HRC	suitable only under restricted conditions	35 m/min	H
GG(G)	suitable only under restricted conditions	120 m/min	K

CuZn	suitable only under restricted conditions	155 m/min	N
Oil	suitable only under restricted conditions		
wet maximum	suitable		