



ISCAR SUMOCHAM drilling head HCP-IQ k7, IC908, Ø DC: 10,2mm



Order data

Order number	231745 10,2
GTIN	7291075333893
Item class	23J

Description

Version:

Vee ground drilling head for precise positioning and stable seating. Angled, **radial stop surfaces** for a significant increase in clamping force due to the cutting forces acting during machining. For productive drilling with **high feed rates**.

HCP-IQ

Main area of application **ISO P** and **ISO K**. **Best possible centring capability**, machining of curved surfaces. **Not for use in ductile materials**.

Note:

Cutting data applies for the base body 5×D. Drill pilot holes exclusively with drilling head of the same type – in particular for drilling heads FCP and QCP-2M. Please observe the application instructions for the base body. Cutting tolerance of the inserts: **k7** (positive toleranced cutting edge diameter).

Designation convention: [type] [Ø D_c]-[addition] [cutting material]

Examples:

No. 231740 6.5 ICP 065 IC908

No. 231742 18.5 ICP 185-2M IC908

No. 231745 18.5 HCP 185-IQ IC908 **The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.**

Technical description

Series	SUMOCHAM
Coating	TiAlN
for base body size	10
Ø D	10.2 mm
Feed f in steel < 900 N/mm ²	0.2 mm/rev.
Number of changes/inserts	2
Iscar item designation	HCP 102-IQ IC908
Geometry	HCP-IQ
Point angle	134 degrees
Manufacturer's designation	HCP 102-IQ IC908
Grade	IC908
Tool material	Carbide
Type of product	Drilling head for boring

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	100 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	55 m/min	P
TOOLOX 33	suitable only under restricted conditions	70 m/min	H
TOOLOX 44	suitable	60 m/min	H
GG(G)	suitable only under restricted conditions	120 m/min	K
CuZn	suitable only under restricted conditions	155 m/min	N

Oil	suitable only under restricted conditions
wet maximum	suitable