



CCMT 09T308, Grade: IC807

Order data

Order number	260173 IC807
GTIN	7291075306422
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Main application	M
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Cutting speed v_c main application	30 - 80 m/min
ISO code indexable insert	CCMT 09T308
Chip breaker	M3M
Feed f	0.08 - 0.3 mm/rev.

Series	ISOTURN
Grade	IC807
Manufacturer's designation	CCMT 09T308-M3M IC807
Type of product	Indexable insert for turning