



DCMT 11T302, Grade: IC807

Order data

Order number	260391 IC807
GTIN	7291075338133
Item class	26B

Description

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cutting conditions	continuous
Corner radius	0.2 mm
Grade	IC807
ISO code indexable insert	DCMT 11T302
Main application	P
Series	ISOTURN
Finishing/roughing assignment	Finishing
Chip breaker	F3P
Feed f	0.08 - 0.3 mm/rev.
Tool material	Carbide
Cutting depth a_p	0.15 - 2 mm
Cutting speed v_c main application	50 - 245 m/min
Number of changes/inserts	2
Manufacturer's designation	DCMT 11T302-F3P IC807
Type of product	Indexable insert for turning

