


DCMT 11T308, Grade: IC807

Order data

Order number	260512 IC807
GTIN	7291075485899
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Main application	P
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.8 - 3 mm
Series	ISOTURN
Cutting conditions	slightly interrupted
Cutting speed v_c main application	50 - 245 m/min
Chip breaker	M3P
ISO code indexable insert	DCMT 11T308
Finishing/roughing assignment	Finishing

Number of changes/inserts	2
Corner radius	0.8 mm
Grade	IC807
Tool material	Carbide
Manufacturer's designation	DCMT 11T308-M3P IC807
Type of product	Indexable insert for turning