


DCMT 11T304, Grade: IC807

Order data

Order number	260511 IC807
GTIN	7291075423761
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Grade	IC807
Cutting depth a_p	0.8 - 3 mm
Chip breaker	M3M
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.3 mm/rev.
Series	ISOTURN
Cutting speed v_c main application	30 - 80 m/min
Corner radius	0.4 mm
Main application	M

ISO code indexable insert	DCMT 11T304
Tool material	Carbide
Cutting conditions	slightly interrupted
Number of changes/inserts	2
Manufacturer's designation	DCMT 11T304-M3M IC807
Type of product	Indexable insert for turning