

Garant
Arbor parallel, SK 40, for cutter head Ø D: 16mm


Order data

| | |
|--------------|---------------|
| Order number | 210575 16 |
| GTIN | 4045197522825 |
| Item class | 21Z |

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

| | |
|-------------------------------|---------|
| for cutter head Ø D | 16 mm |
| Reach L_1 | 30 mm |
| External Ø d_1 | 15.8 mm |
| Overhang dimension A | 49 mm |
| recommended tightening torque | 15 Nm |
| Arbor size | 40 mm |
| Series | TopCut |
| Adapter | SK 40 |

| | |
|-----------------|--------------------------|
| Through-coolant | yes |
| Type of product | Threaded copy mill arbor |