



DNMG 150604, Grade: IC6015



Order data

| | |
|--------------|---------------|
| Order number | 250730 IC6015 |
| GTIN | 7291075341881 |
| Item class | 26B |

Description

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|--------------------------------------|-------------------|
| Main application | M |
| Cutting speed v_c main application | 140 - 300 m/min |
| Finishing/roughing assignment | Finishing |
| Feed f | 0.1 - 0.4 mm/rev. |
| Grade | IC6015 |
| Chip breaker | F3M |
| Cutting depth a_p | 0.1 - 1.5 mm |
| Corner radius | 0.4 mm |
| Cutting conditions | continuous |

| | |
|----------------------------|------------------------------|
| Number of changes/inserts | 4 |
| ISO code indexable insert | DNMG 150604 |
| Tool material | Carbide |
| Manufacturer's designation | DNMG 150604-F3M IC6015 |
| Type of product | Indexable insert for turning |