

Garant
Arbor parallel, SK 40, for cutter head Ø D: 25mm


Order data

Order number	210575 25
GTIN	4045197522849
Item class	21Z

Description

Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

for cutter head Ø D	25 mm
Reach L_1	32 mm
Overhang dimension A	51 mm
External Ø d_1	24.8 mm
recommended tightening torque	35 Nm
Arbor size	40 mm
Series	TopCut
Adapter	SK 40

Through-coolant	yes
Type of product	Threaded copy mill arbor