


DNMG 150608, Grade: IC6025

Order data

Order number	250810 IC6025
GTIN	7291075305104
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Chip breaker	M3M
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
ISO code indexable insert	DNMG 150608
Cutting depth a_p	0.5 - 5 mm
Main application	M
Cutting conditions	slightly interrupted
Feed f	0.17 - 0.5 mm/rev.
Corner radius	0.8 mm

Cutting speed v_c main application	120 - 230 m/min
Grade	IC6025
Tool material	Carbide
Manufacturer's designation	DNMG 150608-M3M IC6025
Type of product	Indexable insert for turning