


DNMG 150608, Grade: IC6025

Order data

Order number	250731 IC6025
GTIN	7291075341911
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Feed f	0.1 - 0.4 mm/rev.
Main application	M
Number of changes/inserts	4
Cutting speed v_c main application	120 - 230 m/min
Grade	IC6025
Cutting conditions	slightly interrupted
Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm

Chip breaker	F3M
ISO code indexable insert	DNMG 150608
Cutting depth a_p	0.1 - 1.5 mm
Manufacturer's designation	DNMG 150608-F3M IC6025
Type of product	Indexable insert for turning