


DNMG 150608, Grade: IC8250

Order data

Order number	250810 IC8250
GTIN	7291075329872
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Feed f	0.15 - 0.6 mm/rev.
Grade	IC8250
Main application	P
Corner radius	0.8 mm
Number of changes/inserts	4
Chip breaker	M3P
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 5 mm
ISO code indexable insert	DNMG 150608

Tool material	Carbide
Cutting conditions	slightly interrupted
Cutting speed v_c main application	150 - 380 m/min
Manufacturer's designation	DNMG 150608-M3P IC8250
Type of product	Indexable insert for turning