

## Garant

### Parallel arbor, without through-coolant, Weldon shank, for cutter head Ø D: 10mm



#### Order data

Order number	210555 10
GTIN	4045197522634
Item class	21Z

#### Description

##### Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out  $\leq 10 \mu\text{m}$**  due to the combination of taper and flat face.

##### Note:

**Maximum milling depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

#### Technical description

Reach $L_1$	24 mm
External $\varnothing d_1$	9.8 mm
for cutter head $\varnothing D$	10 mm
recommended tightening torque	5 Nm
Overall length $L$	75 mm
Shank $\varnothing D_s$	16 mm
Series	TopCut
Adapter	Weldon shank
Type of product	Threaded copy mill arbor

