


**DNMG 150608, Grade: IC8150**

**Order data**

Order number	250731 IC8150
GTIN	7291075319996
Item class	26B

**Description**
**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

ISO code indexable insert	DNMG 150608
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Chip breaker	F3P
Cutting conditions	continuous
Feed f	0.08 - 0.25 mm/rev.
Grade	IC8150
Tool material	Carbide
Main application	P

Cutting speed $v_c$ main application	180 - 400 m/min
Cutting depth $a_p$	0.4 - 3.5 mm
Corner radius	0.8 mm
Manufacturer's designation	DNMG 150608-F3P IC8150
Type of product	Indexable insert for turning