

Garant
GARANT Softcut® 90° shoulder mill MTC, with threaded shank, Ø D / number of teeth Z: 19,7/3mm

Order data

Order number	215570 19,7/3
GTIN	4045197409201
Item class	210

Description
Version:

High precision indexable face mill with irregular pitch for very smooth cutting, very high precision, and very high metal removal rate. **New generation** of high performance indexable face mills **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

Application:

For face milling to large depths, also slotting. General use in all steels including stainless steels.

Spare part:

Pack of insert screws No. 219826 (8IP; 2.2 Nm).

Note:

The insert pocket must be modified when using indexable inserts with a radius greater than 2 mm.

GARANT torque screwdriver TQ No. **211750 size 2.2**, use bit No. **674252 size 8IP**.

Technical description

Pack of insert screws	219826 (8IP; 2.2 Nm)
Cutting edge Ø D _c	19.7 mm
Mounting thread M	M10
Ø D ₁ h6	10.5 mm
Ø D ₂	17.7 mm

Overall length L_{tot}	30 mm
suitable indexable insert	AP.. 1335..
Number of cutting edges Z	3
Circular interpolation milling $\varnothing D_{max}$	37.4 mm
Circular interpolation milling a_p	1.7 mm
Circular interpolation milling $\varnothing D_{min}$	36.4 mm
Ramping angle α_{max}	1.21 degrees
Ramping length L for α_{max}	14.2 mm
Series	Softcut®
$\varnothing D_3$	16.7 mm
Shank type	with threaded shank
Setting angle κ	90 degrees
Milling application	Circular milling
Milling application	Circular milling
Milling application	Ramping
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
Set of insert screws 10-piece	219826
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP