


WNMG 080404, Grade: IC8250

Order data

Order number	252120 IC8250
GTIN	7291075329254
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Corner radius	0.4 mm
Cutting speed v_c main application	150 - 380 m/min
Number of changes/inserts	6
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Feed f	0.15 - 0.6 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Finishing
Chip breaker	M3P

Main application	P
Grade	IC8250
Cutting conditions	slightly interrupted
Manufacturer's designation	WNMG 080404-M3P IC8250
Type of product	Indexable insert for turning