


VNMG 160408, Grade: IC8150

Order data

Order number	251791 IC8150
GTIN	7291075326109
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Chip breaker	F3P
Tool material	Carbide
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.4 - 2.5 mm
Cutting speed v_c main application	180 - 400 m/min
Cutting conditions	continuous
Main application	P
Grade	IC8150
ISO code indexable insert	VNMG 160408

Number of changes/inserts	4
Corner radius	0.8 mm
Feed f	0.08 - 0.24 mm/rev.
Manufacturer's designation	VNMG 160408-F3P IC8150
Type of product	Indexable insert for turning