



WNMG 080408, Grade: IC8150

Order data

Order number	251991 IC8150
GTIN	7291075319361
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cutting speed v_c main application	180 - 400 m/min
Main application	P
Cutting depth a_p	0.4 - 2.5 mm
Feed f	0.08 - 0.25 mm/rev.
Chip breaker	F3P
Finishing/roughing assignment	Finishing
Cutting conditions	continuous
Number of changes/inserts	6
ISO code indexable insert	WNMG 080408

Grade	IC8150
Corner radius	0.8 mm
Tool material	Carbide
Manufacturer's designation	WNMG 080408-F3P IC8150
Type of product	Indexable insert for turning