


DNMG 150612, Grade: IC6025

Order data

Order number	250811 IC6025
GTIN	7291075305098
Item class	26B

Description
Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cutting speed v_c main application	120 - 230 m/min
ISO code indexable insert	DNMG 150612
Chip breaker	M3M
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 5 mm
Corner radius	1.2 mm
Number of changes/inserts	4
Cutting conditions	slightly interrupted
Grade	IC6025

Feed f	0.17 - 0.5 mm/rev.
Main application	M
Tool material	Carbide
Manufacturer's designation	DNMG 150612-M3M IC6025
Type of product	Indexable insert for turning