

**Garant**
**HiPer-Drill cutter insert m7, HB7530, Ø D: 18,3 mm**

**Order data**

Order number	231640 18,3
GTIN	4045197659712
Item class	21M

**Description**
**Version:**

Vee ground cutter inserts for precise positioning and stable seating.  
Concentricity when assembled  $\leq 20 \mu\text{m}$ . For holes up to IT9 accuracy.

**Note:**

Further sizes available on request. Cutting data apply to 5×D drilling bodies.

Use exclusively cutter heads of the same type when drilling pilot holes.

for base body Ø D: 18 mm

Feed f in steel  $< 900 \text{ N/mm}^2$ : 0.28 mm/rev.

**Technical description**

Feed f in steel $< 900 \text{ N/mm}^2$	0.28 mm/rev.
for base body Ø D	18 mm
Ø D	18.3 mm
Number of changes/inserts	1
Grade	HB7530

Tool material	Carbide
Point angle	135 degrees
Number of cutting edges Z	2
Type of product	Cutter insert for boring

---

## Accessories

Torx Plus® screw Drive 8IP1	231999 8IP1
-----------------------------	-------------