



## LOGIQ4FEED high feed rate indexable milling cutter, Plain shank, Ø DC / number of effective cutting edges Z: 32/5



### Order data

Order number	221100 32/5
GTIN	7291075392791
Item class	19D

### Description

#### Version:

Innovative high feed milling system for efficient roughing – especially for machining deep cavities, e.g. in tool and mould making, as well as in the aerospace industry. The twisted shape indexable insert has an auxiliary cutting edge which guarantees a higher metal removal rate during oblique plunging.

#### Spare part:

Pack of insert screws No. **229695 2** (TX7; 0.9 Nm).

### Technical description

Circular interpolation milling Ø D <sub>max</sub>	63 mm
Ø D <sub>3</sub>	24.6 mm
Circular interpolation milling Ø D <sub>min</sub>	56.6 mm
Ramping angle α <sub>max</sub>	1.2 degrees
Ramping length L for α <sub>max</sub>	42.97 mm
Shank Ø D <sub>s</sub> h6	32 mm
Overhang L <sub>1</sub>	120 mm
suitable indexable insert	XNMU040310..
Series	LOGIQ4FEED
Circular interpolation milling a <sub>p</sub>	0.8 mm

Number of cutting edges Z	5
Setting angle $\kappa$	17 degrees
Cutting edge $\varnothing D_c$	32 mm
Through-coolant	yes
Overall length $L_{tot}$	205 mm
Manufacturer's designation	FFX4 ED32-5-120-C32-04
Shank type	Plain shank
Milling application	Plunging
Milling application	Circular milling
Milling application	Ramping
Machining strategy	HPC
Type of product	Copy mills

---

## Accessories

Set of insert screws 5 pieces Type 2	229695 2
--------------------------------------	----------