



LOGIQ4FEED high feed rate indexable milling cutter, Weldon shank, Ø DC / number of effective cutting edges Z: 20/3



Order data

Order number	221101 20/3
GTIN	7291075392760
Item class	19D

Description

Version:

Innovative high feed milling system for efficient roughing – especially for machining deep cavities, e.g. in tool and mould making, as well as in the aerospace industry. The twisted shape indexable insert has an auxiliary cutting edge which guarantees a higher metal removal rate during oblique plunging.

Spare part:

Pack of insert screws No. **229695 2** (TX7; 0.9 Nm).

Technical description

Ramping length L for α_{\max}	19.08 mm
Shank Ø D _s h6	20 mm
Ramping angle α_{\max}	2.7 degrees
Ø D ₃	12.6 mm
Circular interpolation milling a _p	0.8 mm
Cutting edge Ø D _c	25 mm
Through-coolant	yes
Series	LOGIQ4FEED
Overhang L ₁	60 mm
suitable indexable insert	XNMU040310..

Circular interpolation milling $\varnothing D_{\max}$	39 mm
Number of cutting edges Z	3
Overall length L_{tot}	120 mm
Setting angle κ	17 degrees
Circular interpolation milling $\varnothing D_{\min}$	32.6 mm
Manufacturer's designation	FFX4 ED20-3-060-W20-04
Shank type	Weldon shank
Milling application	Plunging
Milling application	Circular milling
Milling application	Ramping
Machining strategy	HPC
Type of product	Copy mills

Accessories

Set of insert screws 5 pieces Type 2	229695 2
--------------------------------------	----------