



LOGIQ4FEED high feed rate indexable milling cutter, Weldon shank, Ø DC / number of effective cutting edges Z: 25/4



Order data

Order number	221101 25/4
GTIN	7291075392784
Item class	19D

Description

Version:

Innovative high feed milling system for efficient roughing – especially for machining deep cavities, e.g. in tool and mould making, as well as in the aerospace industry. The twisted shape indexable insert has an auxiliary cutting edge which guarantees a higher metal removal rate during oblique plunging.

Spare part:

Pack of insert screws No. **229695 2** (TX7; 0.9 Nm).

Technical description

Ø D ₃	17.6 mm
Circular interpolation milling Ø D _{min}	42.6 mm
suitable indexable insert	XNMU040310..
Overhang L ₁	80 mm
Ramping angle α _{max}	1.8 degrees
Through-coolant	yes
Circular interpolation milling a _p	0.8 mm
Shank Ø D _s h6	25 mm
Series	LOGIQ4FEED
Ramping length L for α _{max}	28.64 mm

Setting angle κ	17 degrees
Overall length L_{tot}	140 mm
Cutting edge $\varnothing D_c$	25 mm
Number of cutting edges Z	4
Circular interpolation milling $\varnothing D_{\text{max}}$	49 mm
Manufacturer's designation	FFX4 ED25-4-080-W25-04
Shank type	Weldon shank
Milling application	Plunging
Milling application	Circular milling
Milling application	Ramping
Machining strategy	HPC
Type of product	Copy mills

Accessories

Set of insert screws 5 pieces Type 2	229695 2
--------------------------------------	----------