

**TANGGRIP TNF-IQ inserts, IC808, Groove width w / corner radius R: 3/0,3mm****Order data**

Order number	274222 3/0,3
GTIN	7291075326161
Item class	26A

Description**Version:**

Positive chip breaker. Soft-cutting. Optimal chip control and chip evacuation. Low to medium feed rates.

Application:

For face grooving.

Suitable for:

Blade No. 274202 – 274205.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Corner radius R	0.3 mm
Groove width w	3 mm
Tolerance groove width w	0.05 mm
Feed f	0.1 - 0.15 mm/rev.
Series	TANG-GRIP

Manufacturer's designation	TNF 3P-IQ IC808
Number of changes/inserts	1
Tool material	Carbide
Indexable insert profile	neutral
Finishing/roughing assignment	Finishing
Main application	P
Cutting conditions	slightly interrupted
Chip breaker	P
Cutting speed v_c main application	80 - 150 m/min
Grade	IC808
Type of product	Indexable insert for grooving